

DHI-ARD811

Panic Button (86 box)



- · Supports being mounted in a 86 mm × 86 mm junction box.
- \cdot Works in a wide range of environments with a voltage that is no more than 250 VDC and a current that is no more than 300 mA.
- · Works without a power supply.
- \cdot A reset key is included to quickly reset the device if necessary.

System Overview

The device triggers alarms with the press of a button.

Scene

Ideal for locations where alarms need to be manually triggered in emergencies, such as bank counters, accessible toilets and rooms for the elderly.

Technical Specification		
Port		
Alarm Output	1, NC/NO, 250 VDC, Max. 300 mA	
General		
Operating Temperature	-10 °C to +55 °C (+14 °F to +131 °F)	
Operating Humidity	≤95% (RH)	
Product Dimensions	86.0 mm \times 32.0 mm \times 86.0 mm (3.39" \times 1.26" \times 3.39") (L \times W \times H)	
Net Weight	54 g (0.119 lb)	

Gross Weight	56.5 g (0.124 lb)
Installation	Junction box (86 mm × 86 mm)
Casing Material	ABS
Appearance Color	White case and red button
Certifications	CE
Anti-corrosion Level	Basic Protection
Storage Temperature	-10 °C to +55 °C (+14 °F to +131 °F)
Storage Humidity	≤95% (RH)
Packaging Dimensions	88.0 mm \times 36.0 mm \times 88.0 mm (3.46" \times 1.42" \times 3.46") (L \times W \times H)

Ordering Information		
Туре	Model	Description
Panic Button	DHI-ARD811	Panic Button (86 box)

Installation



























